




Fibre optic diffuse reflection sensor

FT-30-P-A-R8



Application

Function principle	Diffuse reflection sensor
Application	For use in industrial environments

Detection zone

Range with fibre optic amplifier type	OIF
---------------------------------------	-----

OIF

Range fibre optics [mm]	70
-------------------------	----

Operating conditions

Ambient temperature [°C]	-20...80
--------------------------	----------

Mechanical data

Weight [g]	91
Version of sensing head	angled
Sensing head diameter [mm]	8
Total length [mm]	600
Min. bending radius [mm]	30
Fibre arrangement	⓪
Materials	Adapter: PA
Fibre material	glass
Fibre head material	aluminium

E20157



Fibre optic diffuse reflection sensor

FT-30-P-A-R8

Fibre sheath material	PVC
Accessories	
Items supplied	E20353
Remarks	
Pack quantity	1 pcs.