

ZDO6H050MSS0005H11

Alternative artikler: EBC018

Technical drawing of the M12x1 connector showing side and front views with dimensions.

Side View Dimensions:

- Overall length: 125
- Height of the main body: 18
- Height of the mounting flange: 11

Front View Dimensions:

- Overall width: 107
- Overall height: 60
- Height of the mounting flange: 39
- Width of the mounting flange: 4,5
- Thread specification: M12x1

Spesiell egenskap	Fri for silikon; Halogenfri; gullbelagte kontakter
Fri for silikon	ja

Driftsspøenning	[V]	< 60,00 AC / < 75,00 DC
Beskyttelsesklasse		II
Maks. strømbelastning pr. modul/port	[A]	4,00
Maks. nåværende belastning totalt	[A]	12,00

Omgivelsestemperatur	[°C]	-15,00...80,00
Beskyttelse		IP 67



Splitterboks

ZDO6H050MSS0005H11

Mekaniske data

Materialer	TPU
Støpt kroppsmateriale	TPU
Antall porter splitterboks	6
Kontakttype	M12

Merknader

Antall i forpakning	1,00 stk.
---------------------	-----------

Elektrisk tilkobling

Kabel: 5 m, PUR, Halogenfri, svart, Ø 10,4 mm; 12 x 0,5 mm² (63 x Ø 0,1 mm) + 3 x 1,0 mm² (127 x Ø 0,1 mm)

Elektrisk tilkobling - spor

Koblinger: 6 x M12; koding: A; Støpt kropp: TPU; kontakter: gullbelagte; Tiltrekkingsmoment: 0,5 Nm





Splitterboks

ZDO6H050MSS0005H11

Tilkobling

<u>BN</u>	1 (1...6)	C
<u>BU</u>	3 (1...6)	C
<u>GN/YE</u>	5 (1...6)	C
<u>GY/PK</u>	2 (1)	C
<u>RD/BU</u>	2 (2)	C
<u>WH/GN</u>	2 (3)	C
<u>BN/GN</u>	2 (4)	C
<u>WH/YE</u>	2 (5)	C
<u>YE/BN</u>	2 (6)	C
<u>WH</u>	4 (1)	C
<u>GN</u>	4 (2)	C
<u>YE</u>	4 (3)	C
<u>GY</u>	4 (4)	C
<u>PK</u>	4 (5)	C
<u>RD</u>	4 (6)	C

	Lederfarger :
BN =	brun
BU =	blå
GN =	grønn
GY =	grå
PK =	rosa
RD =	rød
WH =	hvit
YE =	gul