


E10420



Connecting cable with socket

ADOGH040MSS0015G04

Article no longer available - archive entry



Application

Special feature	Screened cable
-----------------	----------------

Electrical data

Operating voltage	[V]	< 50 AC / < 60 DC
Protection class		III
Max. current load total	[A]	4

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67

Mechanical data

Weight	[g]	578.8
Dimensions	[mm]	15 x 15 x 46.5
Materials		TPU
Moulded-body material		TPU
Material nut		brass, nickel-plated

Remarks

Pack quantity	1 pcs.
---------------	--------

E10420



Connecting cable with socket


ADOGH040MSS0015G04

Electrical connection


Cable: 15 m, PVC, black, Ø 5 mm, shielded; 4 x 0.25 mm² (32 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated; Tightening torque: 0.5 Nm; Shielded connection cable: screen not connected



Connection



Core colours :
BN = brown
BK = black
BU = blue
WH = white