


Connecting cable with socket

ADOGI020MSS0010K02



Application

Special feature	Halogen-free; Gold-plated contacts; Screened cable; Drag chain suitability
-----------------	--

Electrical data

Operating voltage	[V]	< 30 AC / < 36 DC
Max. current load total	[A]	4; (...40 °C)

Operating conditions

Ambient temperature	[°C]	-40...70
Ambient temperature (moving)	[°C]	-20...50
Protection		IP 67

Mechanical data

Weight	[g]	631
Dimensions	[mm]	14.5 x 14.5 x 43.9
Materials		PUR
Moulded-body material		PUR
Material nut		brass, nickel-plated
Drag chain suitability		yes
Drag chain suitability	bending radius for flexible use	min. 7.5 x cable diameter
	bending radius for fixed installation	min. 10 x cable diameter
	travel speed	max. 5.5 m/s for a horizontal travel length of 5m and max. acceleration of 10 m/s²
	bending cycles	> 5 Mio.
	max. permissible tensile strength	50 N/mm² static
		20 N/mm² dynamic

E12321



Connecting cable with socket

ADOGI020MSS0010K02

Remarks

Pack quantity


1 pcs.

Electrical connection


Cable: 10 m, PUR, Halogen-free, lilac, shielded; 2 x 0.25 mm²

Electrical connection - socket

Connector: 1 x M12, straight; coding: B; Moulded body: PUR; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6 Nm; Shielded connection cable: screen connected



Connection



GN =
RD =

Core colours :
green
red