



Inductive sensor

IEB3003BBPKG/K1/V4A/US-104



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	3
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 50

Application

Special feature	Increased sensing range; Correction factor K = 1; Magnetic-field immune
Magnetic-field immune	yes
Max. magnetic field immunity [mT]	300

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 20
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	2000
Short-circuit protection	yes
Overload protection	yes

Detection zone

Sensing range [mm]	3
Real sensing range Sr [mm]	3 ± 10 %
Operating distance [mm]	0...2.43
Increased sensing range	yes

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 1 / brass: 1 / aluminium: 1 / copper: 1
Hysteresis [% of Sr]	3...15
Switch point drift [% of Sr]	-10...10



Inductive sensor

IEB3003BBPKG/K1/V4A/US-104

Correction factor K = 1		yes	
Operating conditions			
Ambient temperature		[°C]	-40...85
Protection		IP 65; IP 66; IP 67; IP 68; IP 69K	
Tests / approvals			
EMC	EN 61000-4-2 ESD		4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated		10 V/m
	EN 61000-4-4 Burst		2 kV
	EN 61000-4-6 HF conducted		10 V
	EN 55011		class B
Vibration resistance	EN 60068-2-6 Fc		20 g (10...3000 Hz) / 50 sweep cycles, 1 octave per minute, in 3 axes
Shock resistance	EN 60068-2-27 Ea		100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes
Continuous shock resistance	EN 60068-2-27 Ea		40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes
Fast temperature change	EN 60068-2-14 Na		TA = -40 °C; TB = 85 °C; t1 = 30 min; t2 = < 10 s; 50 cycles
Salt spray test	EN 60068-2-52 Kb		severity level 5 (4 test cycles)
MTTF	[years]	1222	
Embedded software included		yes	
UL approval	Ta		-25...70 °C
	Enclosure type		Type 1
	power supply		Limited Voltage/Current
	UL Approval no.		A033
	File number UL		E174191
Mechanical data			
Weight	[g]	17.3	
Housing	threaded type		
Mounting	flush mountable		
Dimensions	[mm]	M8 x 1 / L = 50	
Thread designation	M8 x 1		
Materials	stainless steel (316L/1.4404); sensing face: LCP white; LED window: PEI; lock nuts: stainless steel (316L/1.4404)		
Tightening torque	[Nm]	A = 5 mm: 2 Nm; B: 5 Nm	
Displays / operating elements			
Display	switching status		4 LED, yellow
Accessories			
Items supplied	lock nuts: 2		
Remarks			
Pack quantity	1 pcs.		

Inductive sensor

IEB3003BBPKG/K1/V4A/US-104

Electrical connection - plug

Connector: 1 x M12; coding: A



Connection



Diagrams and graphs

Installation

