


Fibre optic diffuse reflection sensor

FT-00-A-V-E1/0,22m

Article no longer available - archive entry



Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Detection zone

Range with fibre optic amplifier type	OKF; OUF
---------------------------------------	----------

OKF

Range fibre optics [mm]	8
-------------------------	---

OUF

Range fibre optics [mm]	8
-------------------------	---

Operating conditions

Ambient temperature [°C]	-40...290
--------------------------	-----------

Mechanical data

Version of sensing head	straight
-------------------------	----------

Sensing head diameter [mm]	1
----------------------------	---

Sensing head length [mm]	5
--------------------------	---

Total length [mm]	220
-------------------	-----

Min. bending radius [mm]	20
--------------------------	----

Materials	Adapter: ABS
-----------	--------------

Fibre material	glass
----------------	-------

E20484



Fibre optic diffuse reflection sensor

FT-00-A-V-E1/0,22m

Fibre head material	stainless steel (303/1.4305)
Fibre sheath material	aluminium
Remarks	
Pack quantity	1 pcs.