

# E74000



## AS-Interface flat cable

Flat cable 100 meter EPDM ye



Application	
Special feature	Halogen-free
Design	for use of insulation displacement technology
Electrical data	
Operating voltage [V]	26.5...31.6 DC; (Test voltage: 1800 V)
Outputs	
Electrical design	AS-i
Operating conditions	
Ambient temperature [°C]	-40...85
Protection	IP 67
Mechanical data	
Weight [g]	7096
Remarks	
Remarks	100 m form supplied: coiled
Pack quantity	100 m
Electrical connection	
Cable: 100 m, EPDM, Halogen-free, yellow; 2 x 1.5 mm <sup>2</sup>	