



Article no longer available - archive entry

Alternative articles: DX2001

When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available



Application	
Application	universal evaluation and display for all physical units which can be derived from pulse sequences
Electrical data	
Frequency AC [Hz]	47...63
Operating voltage [V]	230 / 115 AC / 24 DC
Current consumption [mA]	200
Operating conditions	
Ambient temperature [°C]	0...45
Protection	IP 44; (on the front)
Mechanical data	
Type of mounting	panel cutout: 91 x 43 mm
Displays / operating elements	
Display	7-segment LED display, red 6-digit 15 mm
Electrical connection	
Connection	