

E89103



Digital display

DISPLAY/DX340/24VAC

Article no longer available - archive entry

replaced by: E89106

No scale drawing available



Application	
Application	universal evaluation and display for all physical units which can be derived from pulse sequences
Electrical data	
Frequency AC [Hz]	47...63
Operating voltage [V]	24 AC
Current consumption [mA]	200
Detection zone	
Sensing range adjustable	no
Operating conditions	
Ambient temperature [°C]	0...45
Protection	IP 44; (on the front)
Mechanical data	
Type of mounting	panel cutout: 91 x 43 mm
Displays / operating elements	
Display	7-segment LED display, red 6-digit 15 mm
Electrical connection	
Connection	

Article no longer available - archive entry

replaced by: E89106