



Article no longer available - archive entry

Alternative article: DX2002 When selecting an alternative article and accessories please note that technical data may differ! – When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available



Application	
Application	universal evaluation and display for all physical units which can be derived from pulse sequences
Electrical data	
Frequency AC	[Hz] 47...63
Operating voltage	[V] 230 / 115 AC / 24 DC
Current consumption	[mA] 200
Outputs	
Analogue current output	[mA] 4...20
Analogue voltage output	[V] 0...10
Operating conditions	
Ambient temperature	[°C] 0...45
Protection	IP 44; (on the front)
Mechanical data	
Type of mounting	panel cutout: 91 x 43 mm
Displays / operating elements	
Display	7-segment LED display, red 6-digit 15 mm 4 x LED, red
Electrical connection	
Connection	

Article no longer available - archive entry

E89121



Digital display

DISPLAY/DY340/ANALOG OUT

Alternative article: DX2002 When selecting an alternative article and accessories please note that technical data may differ! – When selecting an alternative article and accessories please note that technical data may differ!