




Connecting cable with AMP connector


ecomatDisplay/Cable/40p/2.5m



Electrical data		
Operating voltage	[V]	36 DC
Reverse polarity protection		yes
Operating conditions		
Ambient temperature	[°C]	-40...105
Protection		IP 67
Mechanical data		
Weight	[g]	896
Dimensions	[mm]	10 x 10 x 10
Remarks		
Pack quantity		1 pcs.

Electrical connection
Cable: 2.5 m, PVC; FLRY-B; 32 x 0.5 mm ² + 5 x 1.0 mm ² + 3 x 2.5 mm ²

Electrical connection - AMP connector
Connector: 1 x AMP-Junior Timer; Moulded body: PBT, black





Connecting cable with AMP connector

ecomatDisplay/Cable/40p/2.5m

Video	
1: 82	VIDEO3_ GND
2: 90	VIDEO3_ SIGNAL
3: 98	VIDEO0_ GND
4: 106	VIDEO0_ SIGNAL
5: 99	VIDEO1_ GND
6: 107	VIDEO1_ SIGNAL
7: 100	VIDEO2_ GND
8: 108	VIDEO2_ SIGNAL
ifm / Service	
9: 83	IFM0-
10: 91	IFM0+
11: 88	IFM1-
12: 96	IFM1+
13: 89	SERVICE1
14: 97	SERVICE0
CAN	
15: 84	CAN0_ L
16: 92	CAN0_ H
17: 85	CAN1_ L
18: 93	CAN1_ H
19: 86	CAN2_ L
20: 94	CAN2_ H
21: 87	CAN3_ L
22: 95	CAN3_ H
Audio / Head / WAKEUP	
23: 101	AUDIO_IN_R
24: 109	AUDIO_IN_L
25: 102	AUDIO_GND
26: 110	WAKEUP
27: 103	HEAD_OUT_R
28: 111	HEAD_OUT_L
29: 104	AUDIO_R-
30: 112	AUDIO_R+
31: 105	AUDIO_L-
32: 113	AUDIO_L+
VBB / GND / IN / OUT	
33: 114	VBB0
34: 119	VBB15
35: 120	GND
36: 121	VBB30
37: 115	IN0
38: 116	IN1
39: 117	OUT0
40: 118	OUT1