




Through-beam sensor transmitter

OSS-00KG



Product characteristics

Type of light	infrared light
Housing	rectangular

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	20; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880

Detection zone

Transmitter / receiver		transmitter
Range	[m]	< 20
Range adjustable		yes

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 65

Tests / approvals

EMC		EN 60947-5-2
MTTF	[years]	1801

OS5015



Through-beam sensor transmitter

OSS-00KG

Mechanical data		
Weight	[g]	264
Housing		rectangular
Dimensions	[mm]	80 x 28 x 95
Materials		PPO modified
Lens material		glass
Lens alignment		side lens
Displays / operating elements		
Display	operation	1 x LED, yellow
Accessories		
Items supplied	Angle bracket: 1, E20210	
	screwdrivers	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
terminals: ...1.5 mm²; Cable gland: M20 X 1.5		
Connection		

