


EVC924



Ethernet connection cable

VSTGN040MSS00,5K04STGP040--S



Application

Special feature	Free from silicone; Halogen-free; Gold-plated contacts; Screened cable; Drag chain suitability
Design	Ethernet cable, D-coded
Application	Industrial Ethernet; CAT5/CAT5e; 100 Mbit/s; Industrial applications / factory automation
Free from silicone	yes

Electrical data

Operating voltage	[V]	30 AC / 60 DC
Protection class		III
Max. current load total	[A]	1.5

Operating conditions

Ambient temperature	[°C]	-25...90
Note on ambient temperature		Ethernet RJ45 connector: -40...70 °C
Ambient temperature (moving)	[°C]	-25...90
Storage temperature	[°C]	-25...55
Storage humidity	[%]	10...100
Other climatic conditions for storage according to stated class		1K22/ DIN 60721-3-1
Protection		IP 65; IP 67; (M12 plug / RJ45 plug: IP 20)

EVC924



Ethernet connection cable

VSTGN040MSS00,5K04STGP040--S

Mechanical data		
Weight [g]	69.6	
Moulded-body material	TPU / PC	
Material nut	brass, nickel-plated	
Tightening torque [Nm]	Lock nut: 0,6...1,2	
Drag chain suitability	yes	
Drag chain suitability	bending radius for flexible use	min. 10 x cable diameter
	travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s ²
	bending cycles	> 3 Mio.
	torsional strain	± 180 °/m

Remarks	
Remarks	Take into account the maximum value of the counterpart!
Pack quantity	1 pcs.

Electrical connection - plug


Connector: 1 x M12, straight; Moulded body: TPU, black; Locking: brass, nickel-plated; Contacts: gold-plated



Electrical connection

Cable: 0.5 m, PUR, Halogen-free, green, Ø 6.5 mm, shielded; PROFINET Type C; 4 x 0.34 mm² (7 x Ø 0.25 mm)

Connection



Electrical connection - plug

Connector: 1 x RJ45, straight; Moulded body: PC; Contacts: gold-plated

EVC924



Ethernet connection cable

VSTGN040MSS00,5K04STGP040--S

