


E20774



Akrilna optična vlakna na kolutu

ACRYLIC FIBRES ON REEL 50 M



Pogoji okolja

Temperatura okolice	[°C]	-40...70
---------------------	------	----------

Mehanski podatki

Teža	[g]	452,5
Celotna dolžina	[mm]	50000; (konfekcijsko)
Minimalni upogibni polmer	[mm]	30
Razpored vlaken		●
Premer vlaken	[mm]	1
Zunanji premer	[mm]	2,2
Material vlaken		PMMA
Material vlaknaste cevke		PE

Opombe

Embalažna enota	1 Kosov
-----------------	---------