

Priključni kabel

VDOGH040MSS0001A03STGH030MSS

Izdelek ni več na voljo - arhivski vnos



Električni podatki

Obratovalna napetost	[V]	10...30 DC
----------------------	-----	------------

Pogoji okolja

Temperatura okolice	[°C]	-25...90
---------------------	------	----------

Zaščita	IP 67
---------	-------

Mehanski podatki

Mere	[mm]	15 x 15 x 42
------	------	--------------

Materiali	TPU
-----------	-----

Material ulitega dela	TPU
-----------------------	-----

Material slepe matice	medenina, ponikljano
-----------------------	----------------------

Opombe

Embalažna enota	1 Kosov
-----------------	---------

Električni priključek - vtič

Spojnik: 1 x M12, ravno; kodiranje: A; Oblikovano telo: TPU; Zaklep: medenina, ponikljano





Priključni kabel

VDOGH040MSS0001A03STGH030MSS

Električni priključek

Kabel: 1 m, PUR / PVC, oranžno, Ø 5 mm; 3 x 0,34 mm²

Priključek



Električni priključek - vtičnica

Spojnik: 1 x M12, ravno; kodiranje: A; Oblikovano telo: TPU; Zaklep: medenina, ponikljano

