


E74800



Steklena optična vlakna

Fiber optical cable 20m OM2 PUR ST plug



Pogoji okolja

Temperatura okolice	[°C]	-40...80
---------------------	------	----------

Mehanski podatki

Teža	[g]	570
Celotna dolžina	[mm]	20000
Minimalni upogibni polmer	[mm]	77
Razpored vlaken		⊙
Premer jedra	[mm]	0,05
Premer vlaken	[mm]	2 x 0,05
Zunanji premer	[mm]	6
Material vlaken		steklo
Material vlaknaste cevke		PU

E74800



Steklena optična vlakna

Fiber optical cable 20m OM2 PUR ST plug

Pribor	
V sklopu dobave	vtič: 4 x ST, konfekcionirano
Opombe	
Opombe	dobavljena oblika: navito
Embalažna enota	1 Kosov