




AS-Interface automation set for pneumatic valve
actuators

Added Value package AS-i T5



- 1 T5 connection
- 2 target puck spacer гвинти
- 3 solenoid valve
- 4 Кабель для электромагнитного клапана
- 5 FC insulation displacement connector

Product characteristics		
Output function		PNP
Sensing range	[mm]	4
Electrical data		
Max. current consumption from AS-i	[mA]	160
Operating voltage AUX DC	[V]	26.5...31.6; ("supply class 2" to cULus)
Inputs / outputs		
Number of inputs and outputs		Number of digital inputs: 2; Number of digital outputs: 1
Inputs		
Number of digital inputs		2
Outputs		
Number of digital outputs		1
Output function		PNP
Detection zone		
Sensing range	[mm]	4
AS-i classification		
AS-i version		2.1



AS-Interface automation set for pneumatic valve actuators

Added Value package AS-i T5

AS-i profile		S-7.A.E
AS-i I/O configuration	[hex]	7
AS-i ID code	[hex]	A.E

Mechanical data

Weight	[g]	867
Mounting		non-flush mountable
Hole spacing	[mm]	80
Shaft height of valve drive	[mm]	20

Аксессуары

Items supplied	dual sensor for actuator feedback: 1, AC2316 Target pucks: 1, E12517 spacer: 1, E12526 solenoid valve: 1, Bürkert 428623 silencer: 2, 780780N Connection cable: 1, E10844 Flat cable insulation displacement connector: 1, E75471
----------------	---

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Electrical connection - plug




Connection

Connection

1	AS-i +
3	AS-i -

Electrical connection - socket



Outputs

3	external voltage -
4	switching output 1 +