


AS-Interface ClassicLine module

ClassicL45 2DI 2DO T M12

Article no longer available - archive entry

Alternative articles: AC5211

When selecting an alternative article and accessories please note that technical data may differ!



- 1 panel for labelling
2 fixture infrared adapter



Electrical data

Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	150
Max. current load total	[A]	2
Integrated watchdog		yes

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 2; Number of digital outputs: 2
------------------------------	---

Inputs

Number of digital inputs		2
Input circuit of digital inputs		PNP
Sensor supply of the inputs		AS-i
Подача напруги	[V]	18...30; (via flat cable)
Max. total current rating of inputs	[mA]	100
Input current High	[mA]	6...10
Input current Low	[mA]	0...2
Switching level high	[V]	> 11
Digital inputs protected against short circuits		yes



AS-Interface ClassicLine module

ClassicL45 2DI 2DO T M12

Outputs					
Electrical design	AUX				
Number of digital outputs	2				
Circuit	PNP				
Voltage range DC [V]	15...30; (to PELV; via flat cable)				
Max. current load per output [mA]	1000; (utilisation category DC-13 (control of electromagnets): 20 W (IEC 60947-5-1))				
Short-circuit proof	yes				
Electrically separated	yes				
Operating conditions					
Ambient temperature [°C]	-25...70				
Protection	IP 67				
Tests / approvals					
EMC	EN 50295				
AS-i classification					
AS-i version	2.1				
AS-i addressing	IR addressing possible				
Розширений режим адресації	no				
AS-i profile	S-3.0.E				
AS-i I/O configuration [hex]	3				
AS-i ID code [hex]	0.E				
Assignment of the data bits	data bit	D0	D1	D2	D3
	input	1	2	-	-
	socket	I-1	I-2	-	-
	pin	2+4	2+4	-	-
	Output	-	-	1	2
	socket	-	-	O-3	O-4
	pin	-	-	4	4
Mechanical data					
Weight [g]	113.4				
Type of mounting	AS-i interface to FC-E lower parts				
Materials	PBT				
Displays / operating elements					
Display	operation	LED, green			
	errors	LED, red			
	function	LED, yellow			
Аксессуары					
Accessories (optional)	Module lower part				
Remarks					
Remarks	Inputs and outputs must be electrically isolated.				
	Do not connect any of the following points to an external potential:				
	I-, I+, I1, I2				
	The connections are electrically connected with the AS-i cable.				
Pack quantity	1 pcs.				




AS-Interface ClassicLine module

ClassicL45 2DI 2DO T M12

Electrical connection

contact pins to module lower part, FK-E:

Connector: M12; coding: A



	Inputs
1	Sensor supply L+
2+4	data input internally bridged
3	Sensor supply L-
5	not used
	Outputs
1	not used
2	not used
3	external voltage AUX -
4	switching output +
5	not used