




AS-Interface illuminated pushbutton module

c2S-Module 2BI 2LO

Article no longer available - archive entry

Alternative articles: AC2396
When selecting an alternative article and accessories please note that technical data may differ!



- 1 panel for labelling
- 2 LED
- 3 pushbutton 2 / LED 2
- 4 pushbutton 1 / LED 1



Application		
Design		Colour inserts changeable
Application		field installation
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	55
Inputs		
Sensor supply of the inputs		AS-i
Operating conditions		
Ambient temperature	[°C]	-25...60
Storage temperature	[°C]	-40...85
Protection		IP 67
Tests / approvals		
EMC	EN 50295	



AS-Interface illuminated pushbutton module

c2S-Module 2BI 2LO

AS-i classification					
AS-i version	2.1				
Розширений режим адресації	yes				
AS-i master profile	M2; M3; M4				
AS-i profile	S-B.A.E				
AS-i I/O configuration [hex]	B				
AS-i ID code [hex]	A.E				
AS-i certificate	49201				
Assignment of the data bits	data bit	D0	D1	D2	D3
	LED	1	2	-	-
	pushbutton	-	-	1	2
Mechanical data					
Weight [g]	104				
Type of mounting	AS-i interface to FC and SC lower parts				
Materials	PBT				
Displays / operating elements					
Display	operation		LED, green		
	errors		LED, red		
	pushbutton		2 x LED, white		
Аксессуары					
Items supplied	cover support: 2				
	colour inserts: 2, red				
	2, green				
	2, yellow				
	2, blue				
	2, white				
Remarks					
Remarks	The pushbuttons (EAO type 84) provide protection against accidental contact.				
	Housing and pushbuttons can be labelled.				
Pack quantity	1 pcs.				
Electrical connection					
contact pins to module lower part, FK / PG:					