




AS-Interface control cabinet module

SmartL50 4DI 4DO R C



Application		
Application	Встановлення до шафи керування	
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	300
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs	Number of digital inputs: 4; Number of relay outputs: 4	
Inputs		
Number of digital inputs		4
Input circuit of digital inputs	PNP; (type 2 according to IEC 61131-2)	
Sensor supply of the inputs	AS-i	
Подача напруги	[V]	18...30; (DC)
Max. total current rating of inputs	[mA]	200
Input current High	[mA]	6...10
Input current Low	[mA]	0...2
Switching level high	[V]	> 11
Digital inputs protected against short circuits		yes



AS-Interface control cabinet module

SmartL50 4DI 4DO R C

Outputs						
Voltage range DC	[V]	24; (All outputs have to be supplied with the same voltage.: 2 x 24 V DC)				
Voltage range AC	[V]	10...240; (All outputs have to be supplied with the same voltage.: 2 x 240 V AC, same phase conductor)				
Max. current load per output	[mA]	6000; (ohmic resistance)				
Max. current load outputs total	[A]	6; (240 V AC; 24 V DC; ohmic resistance)				
Number of relay outputs		4				
Short-circuit proof		no				
Electrically separated		yes				
Operating conditions						
Ambient temperature	[°C]	-25...60				
Max. relative air humidity	[%]	90; (non condensing)				
Max. height above sea level	[m]	2000				
Protection		IP 20				
Pollution degree		2				
Tests / approvals						
EMC		EN 61000-6-2				
		EN 62026-2				
		EN 50581				
MTTF	[ANN]	279				
AS-i classification						
AS-i version		2.11; 3.0				
AS-i addressing		addressing socket				
Розширений режим адресації		no				
AS-i master profile		M2; M3; M4				
AS-i profile		S-7.0.E				
AS-i I/O configuration	[hex]	7				
AS-i ID code	[hex]	0.E				
Assignment of the data bits		data bit	D0	D1	D2	D3
		input	I-1	I-2	I-3	I-4
		Output	O-1	O-2	O-3	O-4
Mechanical data						
Weight	[g]	275.7				
Type of mounting		mounting on DIN rail				
Materials		PA				
Displays / operating elements						
Display		switching status		LED, yellow I1...I4, O1....O4		
		operation		LED, green AS-i		
		errors		LED, red		
Аксессуары						
Accessories (optional)		connectors				
Remarks						
Pack quantity		1 pcs.				




AS-Interface control cabinet module

SmartL50 4DI 4DO R C

Electrical connection

pin header:

Connection



A+	AS-i +
A-	AS-i -
I+	Sensor supply +24V
I-	Sensor supply 0V
I1...I4	switching input sensor 1...4
O1...O4	switching output relay 1...4
11	relay O1 changeover contact, common
12	relay O1 changeover contact, normally closed contact
14	relay O1 changeover contact, normally open
21	relay O2 changeover contact, common
22	relay O2 changeover contact, normally closed contact
24	relay O2 changeover contact, normally open
33, 34	relay O3 normally open
43, 44	relay O4 normally open