


Lower part for AS-Interface module

ASI-MODUL-UNTERTEIL FK



1 contact pins



Electrical data

Operating voltage	[V]	26.5...31.6 DC
-------------------	-----	----------------

Outputs

Electrical design	AS-i
Contact rating	< 2 A

Operating conditions

Ambient temperature	[°C]	-25...85
Protection	IP 67; (depending on the upper part used: IP 20 / IP 65 / IP 67)	

Mechanical data

Weight	[g]	58.7
Type of mounting	mounting on DIN rail and panel	
Dimensions	[mm]	45 x 80 x 20
Materials	PBT	

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

contact pins in module upper part :

quick mounting technology for AS-i flat cable: