


CR3008



I/O module for mobile machines

R360/MODULE/PWM/4...20mA



Application

Design	housing module
--------	----------------

Electrical data

Operating voltage	[V]	19.2...28.8 DC
Current consumption	[mA]	< 30
Reverse polarity protection		yes

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1
------------------------------	-------------------------------

Inputs

Number of PWM inputs		1; (24 V DC $\pm$ 20 % PWM signal)
PWM frequency inputs	[Hz]	122

Outputs

Number of analogue outputs		1
Analogue current output	[mA]	4...20
Max. load	[Ω]	600

Operating conditions

Ambient temperature	[°C]	-40...85
Note on ambient temperature		wires flexed -5...105 °C wires at rest -30...105 °C
Protection		IP 67

Mechanical data

Weight	[g]	72
Dimensions	[mm]	54 x 34 x 15
Materials		polyamide glass fibre reinforced

Remarks

Pack quantity	1 pcs.
---------------	--------

CR3008



I/O module for mobile machines

R360/MODULE/PWM/4...20mA

Electrical connection

Cable: 0.28 m; / Закінчення жил із кінцевими втулками

input

red	+24 V DC
black	PWM IN
blue	GND

Output

black	4...20 mA
blue	GND

Diagrams and graphs

