

E10440



Connecting cable with socket

ADOAF032MSS0020E03

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	10...30 DC
Protection class		III
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Dimensions	[mm]	17 x 10 x 26
Materials		TPU transparent
Moulded-body material		TPU, transparent
Material nut		brass, nickel-plated
Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green
Remarks		
Pack quantity		1 pcs.

E10440



Connecting cable with socket


ADOAF032MSS0020E03

Electrical connection


Cable: 20 m, PVC, orange, Ø 5 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x M8, angled; coding: A; Moulded body: TPU, transparent; Locking: brass, nickel-plated



Connection



BN =	Core colours :
BK =	brown
BU =	black
	blue