

Connecting cable with socket

ADOAH042VAS0015E03

Article no longer available - archive entry



Electrical data

Operating voltage	[V]	10...30 DC
-------------------	-----	------------

Outputs

Electrical design	PNP
-------------------	-----

Operating conditions

Ambient temperature	[°C]	-25...90
---------------------	------	----------

Protection	IP 67
------------	-------

Mechanical data

Materials	TPU transparent
-----------	-----------------

Moulded-body material	TPU, transparent
-----------------------	------------------

Material nut	stainless steel (1.4404 / 316L)
--------------	---------------------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

E10452



Connecting cable with socket

ADOAH042VAS0015E03

Electrical connection

Cable: 15 m, PVC, orange, Ø 5 mm; 3 x 0.34 mm²

Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU, transparent; Locking: stainless steel (1.4404 / 316L); Tightening torque: 0.5 Nm



Connection



BK =	Core colours :
BN =	black
BU =	brown
	blue