

E10509



Connecting cable with socket

ADOAH042MSS0002E03

Article no longer available - archive entry



Electrical data		
Operating voltage	[M]	10...30 DC
Outputs		
Electrical design		PNP
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Materials		TPU transparent
Moulded-body material		TPU, transparent
Material nut		brass, nickel-plated
Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green
Remarks		
Pack quantity		1 pcs.

E10509



Connecting cable with socket

ADOAH042MSS0002E03

Electrical connection

Cable: 2 m, PVC, orange, Ø 5 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU, transparent; Locking: brass, nickel-plated; Tightening torque: 0.5 Nm



Connection



BN =	Core colours :
BK =	brown
BU =	black
	blue