



Connecting cable with socket

ADOGH040MSS07,5E04

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	< 250 AC / < 300 DC

Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67

Mechanical data		
Dimensions	[mm]	15 x 15 x 43
Materials		TPU
Moulded-body material		TPU
Material nut		brass, nickel-plated

Remarks		
Pack quantity		1 pcs.

Electrical connection		
Cable: 7.5 m, PVC, orange, Ø 5 mm; 4 x 0.25 mm² (32 x Ø 0.1 mm)		

Electrical connection - socket		
Connector: 1 x M12, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated		



E10535



Connecting cable with socket

ADOGH040MSS07,5E04

Connection



BN =	Core colours :	brown
BK =		black
BU =		blue
WH =		white