




Connection cable

VDOGG030--S01,5A03STGH030MSS

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	< 60 AC / < 75 DC
Protection class		III

Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67

Mechanical data		
Materials		TPU
Moulded-body material		TPU
Material nut		brass, nickel-plated

Remarks		
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated



E10557




Connection cable

VDOGG030--S01,5A03STGH030MSS

Electrical connection

Cable: 1.5 m, PUR / PVC, orange, Ø 5 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Connection



Electrical connection - socket

Connector: 1 x M8, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated

