

# E10615



## Connecting cable with socket

ADOAF032ZDS0005A03

Article no longer available - archive entry



### Electrical data

|                   |     |            |
|-------------------|-----|------------|
| Operating voltage | [V] | 10...30 DC |
| Protection class  |     | III        |

### Outputs

|                   |     |
|-------------------|-----|
| Electrical design | PNP |
|-------------------|-----|

### Operating conditions

|                     |      |          |
|---------------------|------|----------|
| Ambient temperature | [°C] | -25...90 |
| Protection          |      | IP 67    |

### Mechanical data

|                       |      |              |
|-----------------------|------|--------------|
| Dimensions            | [mm] | 17 x 10 x 26 |
| Materials             |      | PUR          |
| Moulded-body material |      | PUR          |
| Material nut          |      | diecast zinc |

### Displays / operating elements

|         |                  |                 |
|---------|------------------|-----------------|
| Display | switching status | 1 x LED, yellow |
|         | operation        | 1 x LED, green  |

### Remarks

|               |        |
|---------------|--------|
| Pack quantity | 1 pcs. |
|---------------|--------|

# E10615



## Connecting cable with socket

ADOAF032ZDS0005A03

### Electrical connection

Cable: 5 m, PUR / PVC, black, Ø 5 mm; 3 x 0.34 mm<sup>2</sup> (42 x Ø 0.1 mm )

### Electrical connection - socket

Connector: 1 x M8, angled; coding: A; Moulded body: PUR; Locking: diecast zinc



### Connection



|      |                |
|------|----------------|
| BN = | Core colours : |
| BK = | brown          |
| BU = | black          |
|      | blue           |