


Jumper cable with valve plug

VVSAC041MSS0003B03STGH030MSS

Article no longer available - archive entry



1 grey

Electrical data

Operating voltage	[V]	< 24 AC/DC
-------------------	-----	------------

Operating conditions

Ambient temperature	[°C]	-25...90
Protection		IP 65

Mechanical data

Materials	TPU
Moulded-body material	TPU
Material nut	brass, nickel-plated

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated



E10667




Jumper cable with valve plug

VVSAC041MSS0003B03STGH030MSS

Electrical connection

Cable: 3 m, PUR; 3 x 0.34 mm²

Connection



Electrical connection - socket

Connector: 1 x valve type A DIN, angled; Moulded body: TPU; Locking: brass, nickel-plated

