


E10925



Connection cable

VDOGG030--S0001H03STGF030MSS

Article no longer available - archive entry



Application

Special feature	Halogen-free
-----------------	--------------

Electrical data

Operating voltage	[V]	10...55 DC
Protection class		III

Operating conditions

Ambient temperature	[°C]	-25...90
Protection		IP 65

Mechanical data


Materials	TPU
Moulded-body material	TPU
Material nut	brass, nickel-plated

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M8, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated



E10925



Connection cable

VDOGG030--S0001H03STGF030MSS

Electrical connection

Cable: 1 m, Halogen-free; 3 x 0.34 mm²

Connection



Electrical connection - socket

Connector: 1 x M8, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated

