

## Connection cable

VDOG030MSS00,3H03STGF030MSS

Article no longer available - archive entry



## Application

Special feature

Halogen-free

## Electrical data

Operating voltage

[V]

10...55 DC

Protection class

III

## Operating conditions

Ambient temperature

[°C]

-25...90

Protection

IP 67

## Mechanical data

Materials

TPU

Moulded-body material

TPU

Material nut

brass, nickel-plated

## Remarks

Pack quantity

1 pcs.

## Electrical connection - plug

Connector: 1 x M8, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated



# E10927



## Connection cable

VDOGF030MSS00,3H03STGF030MSS

### Electrical connection

Cable: 0.3 m, TPU, Halogen-free; 3 x 0.34 mm<sup>2</sup> (42 x Ø 0.1 mm )

### Connection



### Electrical connection - socket

Connector: 1 x M8, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated

