

E10966




Connecting cable with socket

ADOGH050MSS0002H05

Article no longer available - archive entry

Alternative articles: EVC070
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Special feature		Free from silicone; Halogen-free; Gold-plated contacts
Free from silicone		yes
Electrical data		
Operating voltage	[V]	< 30 AC / < 36 DC
Max. current load total	[A]	4
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 68
Mechanical data		
Dimensions	[mm]	15 x 15 x 43
Materials		TPU
Moulded-body material		TPU
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

E10966



Connecting cable with socket

ADOGH050MSS0002H05

Electrical connection


Cable: 2 m, PUR, Halogen-free, black, Ø 5.5 mm; 5 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.5 Nm



Connection



Core colours :
BK = black
BN = brown
BU = blue
GY = grey
WH = white