




Connecting cable with socket

ADOAA030MSS0010B03

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	< 250 AC / < 300 DC
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Materials		TPU
Moulded-body material		TPU
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

Electrical connection

Cable: 10 m, PUR, orange, Ø 5.2 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x 1/2", angled; coding: C; Moulded body: TPU; Locking: brass, nickel-plated




E10262



Connecting cable with socket

ADOAA030MSS0010B03

Connection



GN =	Core colours :
RD/BK =	green
RD/WH =	red/black
	red/white