

E10295



Connecting cable with socket

ADOAH040MSS0002F03

Article no longer available - archive entry

Alternative articles: E10909

When selecting an alternative article and accessories please note that technical data may differ!



Electrical data

Operating voltage [V] < 250 AC / < 300 DC

Operating conditions

Ambient temperature [°C] -25...90

Protection IP 67

Mechanical data

Dimensions [mm] 27 x 15 x 39

Materials TPU

Moulded-body material TPU

Material nut brass, anti-spatter

Remarks

Pack quantity 1 pcs.

E10295



Connecting cable with socket

ADOAH040MSS0002F03

Electrical connection

Cable: 2 m, PVC, orange, Ø 5 mm; cross-linked; 3 x 0.34 mm² (19 x Ø 0.15 mm)

Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU; Locking: brass, anti-spatter; Tightening torque: 0.5 Nm



Connection



BN =
BK =
BU =

Core colours :
brown
black
blue