




Splitter box

ProcessLine SB V4A 25m



Electrical data		
Operating voltage	[V]	10...36 DC
Protection class		III
Max. current load per module/slot	[A]	4
Max. current load total	[A]	6
Outputs		
Electrical design		PNP
Operating conditions		
Ambient temperature	[°C]	-5...70



Splitter box

ProcessLine SB V4A 25m

Protection	IP 69K; (To ensure the protection rating unused sockets must be covered with the supplied protective caps.; Tightening torque: 1,3 Nm +/- 0,1 Nm)
------------	---

Tests / approvals

MTTF	[ANN]	2487
------	-------	------

Mechanical data

Weight	[g]	5376
Dimensions	[mm]	Ø 137.3 / L = 72
Materials	threaded bush: stainless steel (1.4404 / 316L); LED-Fenster: PC; O-ring: EPDM; Protective cap: PP	
Moulded-body material	stainless steel	
Number of ports splitter box	8	
Connector type	M12	

Displays / operating elements

Display	switching status	16 x LED, yellow
	operation	1 x LED, green

Аксессуары

Items supplied	захисні заглушки: M12
----------------	-----------------------

Remarks


Remarks	external voltage supply according to PELV
Pack quantity	1 pcs.

Electrical connection

Cable: 25 m, PUR / PVC, black, Ø 11 mm; 3 x 0.75 mm² + 16 x 0.34 mm²

Electrical connection - slot

Connector: 8 x M12; coding: A; Moulded body: stainless steel



Splitter box

ProcessLine SB V4A 25m

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
GN =	green
GY =	grey
PK =	pink
RD =	red
VT =	lilac
WH =	white
YE =	yellow

E11847

Splitter box

ProcessLine SB V4A 25m

