

E11903




Connecting cable with plug

ASTAH050MSS0002H05

Article no longer available - archive entry

Alternative articles: EVC095
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Special feature		Free from silicone; Halogen-free; Gold-plated contacts
Free from silicone		yes
Electrical data		
Operating voltage	[V]	< 30 AC / < 36 DC
Max. current load total	[A]	4
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Dimensions	[mm]	39 x 15 x 30
Materials		TPU
Moulded-body material		TPU
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

E11903



Connecting cable with plug


ASTAH050MSS0002H05

Electrical connection


Cable: 2 m, PUR, Halogen-free, black, Ø 5 mm; 5 x 0.34 mm² (43 x Ø 0.1 mm)

Electrical connection - plug

Connector: 1 x M12, angled; coding: A; Moulded body: TPU; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.5 Nm



Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
GY =	grey
WH =	white