

E11249



Connecting cable with socket

ADOAA050MSS0010H04



Application		
Special feature		Halogen-free
Electrical data		
Operating voltage	[V]	< 300 AC
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Weight	[g]	322.7
Materials		TPU
Moulded-body material		TPU
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

E11249



Connecting cable with socket

ADOAA050MSS0010H04

Electrical connection


Cable: 10 m, PUR, Halogen-free, black, Ø 4.7 mm; 4 x 0.34 mm² (43 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x 1/2", angled; coding: C; Moulded body: TPU; Locking: brass, nickel-plated



Connection



BK = Core colours :
BN = black
BU = brown
WH = blue
WH = white