


E12491



Ethernet connection cable

VSTGN040ZDS0005L04STGP040--S



Application		
Special feature		Screened cable
Design		Ethernet cable, D-coded
Application		cross-over patch cable; patch cable
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67; IP 20; (M12 plug / RJ45 plug)
Mechanical data		
Weight	[g]	367.2
Materials		TPU / PA
Moulded-body material		PA / TPU
Material nut		diecast zinc, nickel-plated
Remarks		
Pack quantity		1 pcs.

Electrical connection - plug M12

Connector: 1 x M12, straight; coding: D; Moulded body: PA; Locking: diecast zinc, nickel-plated; Tightening torque: 0.7...0.9 Nm



E12491



Ethernet connection cable

VSTGN040ZDS0005L04STGP040--S

Electrical connection

Cable: 5 m, PVC, green, Ø 6.5 mm, shielded; 2 x 2 x 0.38 mm²

Connection



Electrical connection - plug RJ45

Connector: 1 x RJ45, straight; Moulded body: TPU

