

E18317



Connection cable

VDOGH040MKS0005E04STGH040MKS



Application

Special feature	Free from silicone; Halogen-free; Gold-plated contacts
Free from silicone	yes

Electrical data

Operating voltage	[V]	< 250 AC / < 300 DC
Max. current load total	[A]	3

Operating conditions

Ambient temperature	[°C]	-25...85
Protection		IP 68

Mechanical data

Weight	[g]	204.116
Materials		PVC
Moulded-body material		PVC
Material nut		zinc, epoxy coated

Remarks

Pack quantity	1 pcs.
---------------	--------



Connection cable

VDOGH040MKS0005E04STGH040MKS

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Moulded body: PVC; Locking: zinc, epoxy coated; Contacts: gold-plated; Tightening torque: 0.7...0.9 Nm



Electrical connection

Cable: 0.3 m, PVC, Halogen-free, yellow, Ø 4.7 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Connection



Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Moulded body: PVC; Locking: zinc, epoxy coated; Contacts: gold-plated; Tightening torque: 0.7...0.9 Nm

