

Fibre optic diffuse reflection sensor

FT-00-A-A-M6/0,8M

Article no longer available - archive entry



Application

Function principle

Diffuse reflection sensor

Application

Висока стійкість до температури; Міцне виконання
для використання у важких умовах експлуатації

Detection zone

Range with fibre optic
amplifier type

OKF; OUF

OKF

Range fibre optics

[mm]

40

OUF

Range fibre optics

[mm]

40

Operating conditions

Ambient temperature

[°C]

-40...290

Mechanical data

Version of sensing head

straight

Sensing head thread

M6

Sensing head length

[mm]

35

Total length

[mm]

800

Min. bending radius

[mm]

20

E20067



Fibre optic diffuse reflection sensor

FT-00-A-A-M6/0,8M

Materials	Adapter: ABS
Fibre material	glass
Fibre head material	aluminium
Fibre sheath material	aluminium
Remarks	
Pack quantity	1 pcs.