


Fibre optic through-beam sensor

FE-30-A-A-M6



Application

Function principle	Through-beam sensor
Application	Висока стійкість до температури; Міцне виконання для використання у важких умовах експлуатації

Detection zone

Range with fibre-optic amplifier type	OIF
---------------------------------------	-----

OIF

Range of fibre optics [mm]	300
----------------------------	-----

Operating conditions

Ambient temperature [°C]	-40...290
--------------------------	-----------

Mechanical data

Weight [g]	106
Version of sensing head	straight
Sensing head thread	M6
Total length [mm]	600
Min. bending radius [mm]	30; (for fixed installation)
Fibre arrangement	
Materials	Adapter: PA
Fibre material	glass
Fibre head material	aluminium

E20160



Fibre optic through-beam sensor

FE-30-A-A-M6

Fibre sheath material	aluminium
Аксессуары	
Items supplied	hexagon nuts: 4 x M6, stainless steel
	tooth lock washers: 4
	knurled nut: 1 x M30
Remarks	
Pack quantity	1 pcs.