


Fibre optic through-beam sensor

FE-30-P-A-M6



Application

Function principle

Through-beam sensor

Application

Для використання у промисловості

Detection zone

Range with fibre-optic
amplifier type

OIF

OIF

Range of fibre optics

[mm]

300

Operating conditions

Ambient temperature

[°C]

-20...80

Mechanical data

Weight

[g]

98.5

Version of sensing head

straight

Sensing head thread

M6

Sensing head length

[mm]

35

Total length

[mm]

600

Min. bending radius

[mm]

30

Fibre arrangement



Materials

Adapter: PA

Fibre material

glass

E20164



Fibre optic through-beam sensor

FE-30-P-A-M6

Fibre head material	aluminium
Fibre sheath material	PVC
Аксессуары	
Items supplied	hexagon nuts: 4 x M6, stainless steel
	tooth lock washers: 4
	knurled nut: 1 x M30
Remarks	
Pack quantity	1 pcs.