




Fibre optic through-beam sensor

FE-30-A-A-M6/3M



Application	
Function principle	Through-beam sensor
Application	Висока стійкість до температури; Міцне виконання для використання у важких умовах експлуатації
Detection zone	
Range with fibre-optic amplifier type	OIF
OIF	
Range of fibre optics [mm]	192
Operating conditions	
Ambient temperature [°C]	-40...290
Mechanical data	
Weight [g]	278.5
Version of sensing head	straight
Sensing head thread	M6
Total length [mm]	3000
Min. bending radius [mm]	30; (for fixed installation)
Fibre arrangement	●
Materials	Adapter: PA
Fibre material	glass
Fibre head material	aluminium

E20229



Fibre optic through-beam sensor

FE-30-A-A-M6/3M

Fibre sheath material	aluminium
Аксессуары	
Items supplied	hexagon nuts: 4 x M6, stainless steel
	tooth lock washers: 4
	knurled nut: 1 x M30
Remarks	
Pack quantity	1 pcs.