


## Fibre optic through-beam sensor

FE-30-A-A-R3/3m

Article no longer available - archive entry



## Application

Function principle

Through-beam sensor

## Detection zone

Range with fibre-optic  
amplifier type

OIF

## OIF

Range of fibre optics

[mm]

64

## Operating conditions

Ambient temperature

[°C]

-40...290

## Mechanical data

Version of sensing head

angled

Total length

[mm]

3000

Min. bending radius

[mm]

30

Materials

Adapter: PA

Fibre material

glass

Fibre head material

aluminium

Fibre sheath material

aluminium

## Remarks

Pack quantity

1 pcs.