




Fibre optic through-beam sensor

FE-18-P-A-M4

phase-out article



Application		
Function principle	Through-beam sensor	
Application	Для використання у промисловості	
Detection zone		
Range with fibre-optic amplifier type	OGF	
OGF		
Range of fibre optics	[mm]	80
Operating conditions		
Ambient temperature	[°C]	-20...80
Mechanical data		
Weight	[g]	50
Version of sensing head	straight	
Sensing head thread	M4	
Sensing head length	[mm]	15
Total length	[mm]	600
Min. bending radius	[mm]	20
Fibre arrangement		
Materials	Adapter: PPE	

E20387



Fibre optic through-beam sensor

FE-18-P-A-M4

Fibre material	glass
Fibre head material	aluminium
Fibre sheath material	PVC
Аксессуары	
Items supplied	hexagon nuts: 4 x M4
	tooth lock washers: 4
Remarks	
Pack quantity	1 pcs.