

## Fibre optic through-beam sensor

FE-00-S-V-M4/0,4M

Article no longer available - archive entry



## Application

Function principle

Through-beam sensor

## Detection zone

Range with fibre-optic  
amplifier type

OKF; OUF

## OKF

Range of fibre optics

[mm]

120

## OUF

Range of fibre optics

[mm]

120

## Operating conditions

Ambient temperature

[°C]

-20...80

## Mechanical data

Version of sensing head

straight

Sensing head thread

M4

Sensing head length

[mm]

15

Total length

[mm]

400

Min. bending radius

[mm]

20

Materials

Adapter: ABS

Fibre material

glass

E20394



Fibre optic through-beam sensor

FE-00-S-V-M4/0,4M

|                       |                              |
|-----------------------|------------------------------|
| Fibre head material   | stainless steel (303/1.4305) |
| Fibre sheath material | silicone                     |
| Remarks               |                              |
| Pack quantity         | 1 pcs.                       |