



Process adapter hygienic pipe fitting


ADAPT IFM-DIN11851/DN50 (2)

Article no longer available - archive entry

Alternative articles: E33713

When selecting an alternative article and accessories please note that technical data may differ!

The alternative article requires the use of a new sensor with Aseptoflex Vario external thread



- 1 Aseptoflex thread
2 Aseptoflex sealing edge

EC 1935/2004 FCM 

Application

Pressure rating [bar] 25

Tests / approvals

Pressure Equipment Directive A possible classification to PED depends on the application and has to be carried out by the user / operator.

Safety instructions The compatibility between medium and product material has to be checked in all applications.

Mechanical data

Weight [g]	349.5
Materials	stainless steel (1.4404 / 316L)
Sensor connection	Aseptoflex
Process connection	hygienic pipe fitting DN50 (2") DIN 11851
Surface characteristics Ra/Rz of the wetted parts	0.4 / 4
Hygienic equipment class to DIN 11866	H4

Remarks

Pack quantity 1 pcs.