


Universal process adapter

ADAPT UNI RD52



- 1 O-ring 30 x 2, FKM
2 O-ring 36 x 3, EPDM

Application

Pressure rating [bar] 16

Tests / approvals

Pressure Equipment Directive

A possible classification to PED depends on the application and has to be carried out by the user / operator.

Safety instructions

The compatibility between medium and product material has to be checked in all applications.

Mechanical data

Weight [g]	378
Materials (wetted parts)	stainless steel (1.4435 / 316L) ; surface characteristics : Ra<0,4 / Rz 4
Sensor connection	G 1 Aseptoflex Vario
Process connection	universal process adapter Rd 52
Sealing	Gasket

E33341



Universal process adapter

ADAPT UNI RD52

Hygienic equipment class to DIN 11866	H4
Аксессуары	
Items supplied	O-ring: 24 x 2, EPDM, FDA compliant, E30054
	O-ring: 30 x 2, FKM
	O-ring: 36 x 3, EPDM, FDA compliant
Accessories (optional)	O-ring: 24 x 2, FKM, FDA compliant, E30123
	sealing ring, PEEK, FDA compliant, E30124
Remarks	
Pack quantity	1 pcs.