




Welding thermowell for temperature sensors

THERMOWELL, D6/WELD-IN/L=300



EC 1935/2004 EHEDG Certified



Application		
Design		for temperature sensors EL = 350 mm
Pressure rating	[bar]	400
Accuracy / deviations		
Max. permissible flow velocity	[m/s]	13
Mechanical data		
Weight	[g]	1577.5
Materials		stainless steel (1.4404 / 316L)
Sensor connection		1/2" NPS Ø 6 mm suitable for G1/2 and 1/2" NPT
Process connection		welding adapter Ø 38,1 mm
Installation length EL	[mm]	267
Bore length BL	[mm]	304.8
Remarks		
Pack quantity		1 pcs.