




Connecting cable with socket

ADOAH050MSN0005A05

Article no longer available - archive entry



Application		
Application		Ex zone 1
Electrical data		
Operating voltage	[V]	10...30 DC
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Safety classification		
Max. internal capacitance	[nF]	0.38
Max. internal inductance	[µH]	2.95
Mechanical data		
Dimensions	[mm]	27 x 15 x 39
Materials		TPU
Moulded-body material		TPU
Material nut		brass, nickel-plated
Remarks		
Remarks	When using sockets in hazardous areas (ATEX) there are special requirements regarding wiring. The requirements of the applicable installation regulations must be absolutely adhered to by the user on his own responsibility.	
Pack quantity		1 pcs.

# E40076



## Connecting cable with socket


ADOAH050MSN0005A05

### Electrical connection


Cable: 5 m, PUR / PVC, blue, Ø 6 mm; 5 x 0.34 mm<sup>2</sup> (42 x Ø 0.1 mm )

### Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU; Locking: brass, nickel-plated



### Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
GY =	grey
WH =	white